



ASSEMBLY INSTRUCTIONS 1100ml BOTTLES 2 pack

- 1) After filling, insert sealing plug to full depth, screw the cap to the recommended torque

Recommended torques:

1100ml aluminum bottle type agrochem 42 with caps with aluminum liner and plug.
Between 44 and 62 inch per lbs.

Recommended capping tool. Item # MCAPR03. The torque is preset at 50 inch per lbs.
Custom chuck. Item # ADAPT40

1100ml aluminum bottle type chem. 50 with caps with aluminum liner and plug.
89 inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT50

1100ml aluminum bottle type chem. 50 with caps with Teflon liner.
Between 53 and 71 inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT50

1100ml aluminum bottle type Plus 45 with caps with Teflon liner.
Between 44 and 62 inch per lbs.

Recommended capping tool. Item # MCAPR03. The torque is preset at 50 inch per lbs.
Custom chuck. Item # ADAPT40

- 2) Tape along slot of carton bottom with 2" wide (48mm) p.s. Scotch 375 Clear. Arrows up. The tape extends a minimum of 3" on each end of the box.
- 3) Fold both scored lines of the liners to create 2 cells.
- 4) Place liner(s) in the carton.



- 5) Place filled bottles in carton keeping the arrow sign up.
- 6) Seal flaps with the same tape as previously used for the bottom being careful not to cover arrows.

Labeling and marking are the shipper's responsibility.

Elemental Container assumes no responsibility for the package integrity or compliance to the U.N. hazardous goods regulations unless all package components are assembled per the above instructions and supplied by Elemental Container.

Product compatibility with the aluminum container is the customer's responsibility and must be in accordance with the Packaging instructions of the 49CFR. Container compliance is predicated on a product maximum density of 1.2 (H₂O = 1.0), a nominal fill and correct assembly of the polyethylene plug (if used) and the closure tightened to the recommended torque.