



Assembly Instruction for 160ML TYPE PLUS 32

ALUMINUM BOTTLES U.N. APPROVED AS SINGLE PACKAGINGS (1B1).

This bottle has been tested and approved with the following components:

Option 1 : Certificate 1093 Index 5. Group I, II, III

1/ ALUMINUM BOTTLE

2/ LDPE PLUG

3/ PP CAP WITH ALPE/PEE LINER

After filling, insert the sealing plug to full depth by pushing it down, screw the cap to the following recommended torque: Between 27 and 44 Inch per lbs.

Recommended capping tool. Item # MCAPR02. Torque is preset at 38 inch per lbs.

Custom chuck. Item # ADAPT32

Option 2 : Extension 001 Index 0 to Certificate 1093. I, II, III

1/ ALUMINUM BOTTLE

2/ PP CAP WITH PTFE (Teflon) LINER

After filling, screw the cap to the following recommended torque: Between 27 and 44 Inch per lbs.

Recommended capping tool. Item # MCAPR02. Torque is preset at 38 inch per lbs.

Custom chuck. Item # ADAPT32

Labeling and marking are the shipper responsibility.

Elemental Container assumes no responsibility for the package integrity or compliance to the U.N. hazardous goods regulations unless all package components are assembled per the above instructions and supplied by Elemental Container.

Product compatibility with the aluminum is the customer responsibility and must be in accordance with the Packaging instructions of the 49CFR. Container compliance is predicated on a product maximum density of 1.2 (H₂O = 1.0).

Elemental Container Inc . 860 Springfield Road South . Union, New Jersey 07083 . USA
Telephone 908.687.7720 . 800. 577.7624 . Fax 908.687.5157 . www.aluminumbottles.com

Last update 09/14/17



UN certificates are available upon request.

NON U.N. CLOSURE OPTIONS

Because of the large number of bottles and closure systems and the cost of testing and maintaining certificates, we have certified the most used closures.

A closure that hasn't been tested for the U.N. requirements can be used for nonhazardous products. Even if they have not been tested it doesn't mean that they are inferior in any ways. Ask your sales rep if you need to have the bellow closure system certified.

1/ ALUMINUM BOTTLE

2/ PP CAP WITH ALPE/PEE LINER

After filling, screw the cap to the following recommended torque: Between 27 and 44 Inch per lbs.

Recommended capping tool. Item # MCAPR02. Torque is preset at 38 inch per lbs.

Custom chuck. Item # ADAPT32

1/ ALUMINUM BOTTLE

2/ LDPE PLUG

3/ PP CAP WITH PTFE (Teflon) LINER

After filling, insert the sealing plug to full depth by pushing it down, screw the cap to the following recommended torque: Between 35 and 44 Inch per lbs.

Recommended capping tool. Item # MCAPR02. Torque is preset at 38 inch per lbs.

Custom chuck. Item # ADAPT32